



DieselTest

Pump info

Part number: 0445010142
Test type: CR/CP1H3/R70/10-89S
Steps: 18
Swap pressuare, kPa: 450
Reverse pressuare, kPa: 50

Client profile

Result

Clean run

Supply 12V; Rotation R; Pressuare 0 MPa; Speed 1500 RPM;
Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;

No Flow 1
No Flow 2
HP 0

Warm up

Supply 12V; Rotation R; Pressuare 25 MPa; Speed 2700 RPM;
Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;

No Flow 1
No Flow 2
HP 0

zme takt. 1

Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM;
Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;

No Flow 1
No Flow 2
HP 0

zme takt. 2	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt. 3	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt. 4	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt. 5	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt. 6	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt.7	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
------------	---	--

zme takt.8	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
------------	---	--

zme takt.9	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
------------	---	--

zme takt.10	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt.11	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

zme takt.12	Supply 12V; Rotation R; Pressuare 0 MPa; Speed 2500 RPM; Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
-------------	---	--

kenn . 2	Supply 12V; Rotation R; Pressuare 50 MPa; Speed 2700 RPM; Flow 1 Max 118.4; Flow 1 Min 85.6; Flow 2 Max 0; Flow 2 Min 0;	No Flow 1 No Flow 2 HP 0
----------	---	--

kenn . 3	Supply 12V; Rotation R; Pressuare 50 MPa; Speed 2700 RPM;	No Flow 1
	Flow 1 Max 75.3; Flow 1 Min 47.9; Flow 2 Max 0; Flow 2 Min 0;	No Flow 2
		HP 0

kenn . 4	Supply 12V; Rotation R; Pressuare 50 MPa; Speed 2700 RPM;	No Flow 1
	Flow 1 Max 27; Flow 1 Min 6.8; Flow 2 Max 0; Flow 2 Min 0;	No Flow 2
		HP 0

Relax	Supply 12V; Rotation R; Pressuare 20 MPa; Speed 500 RPM;	No Flow 1
	Flow 1 Max 0; Flow 1 Min 0; Flow 2 Max 0; Flow 2 Min 0;	No Flow 2
		HP 0

